

Rittal – The System.

Faster – better – everywhere.



IT 5302.042

19인치 케이블 브리지, 가변 깊이

상태: 2026. 2. 11 (원천: rittal.com/kr-ko)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

IT 5302.042 - 19인치 케이블 브리지, 가변 깊이

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

특징

주문 번호	IT 5302.042
장점	<p>Cable entry at the front via brush strip for thermal partitioning of the cable entry zone</p> <p>Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear</p> <p>Fully depth-variable with versatile, infinitely adjustable extension of the cable link</p> <p>Prevents incorrect airflow by partitioning the transition</p> <p>Open at the top for easy retrofitting, even with cables already inserted</p> <p>Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip</p>
재료	<p>강판</p> <p>브러시 스트립: 플라스틱, UL 94-V0</p>
표면 처리	분사 도장
색상	RAL 9005
제공 범위	<p>Cable link</p> <p>브러시 스트립</p>
설치 옵션	전면 및 후면 19"(482.6mm) 장착 레벨 사이에 고정하기 위한 용도
레벨 간격	500 - 750 mm
높이 단위	1 U

특징

부하 용량(정적 하중)	150 N
적합한:	인클로저에 관계없이 다양하게 장착
참고 사항	Assembly parts should be ordered separately
포장 단위	1 개
PCF/VE(크래들-게이트)	PCF-Wert 18,78 kg Co ² e
관세 번호	73269098