Rittal – The System.

Faster - better - everywhere.





IT 5302.042 19인치 케이블 브리지, 가변 깊이

상태: 2025. 11. 26 (원천: rittal.com/kr-ko)



IT 5302.042 - 19인치 케이블 브리지, 가변 깊이

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

특징

주문 번호	IT 5302.042
장점	Cable entry at the front via brush strip for thermal partitioning of the cable entry zone
	Direct cable routing between the patch level and component
	with rear installation, optimum cable routing with switch
	mounted at the rear
	Fully depth-variable with versatile, infinitely adjustable
	extension of the cable link
	Prevents incorrect airflow by partitioning the transition
	Open at the top for easy retrofitting, even with cables already inserted
	Cable link extendible upwards by 1 U, by using an additional
	cable entry panel with brush strip
재료	강판
	브러시 스트립: 플라스틱, UL 94-V0
표면 처리	분사 도장
색상	RAL 9005
제공 범위	Cable link
	브러시 스트립
설치 옵션	전면 및 후면 19"(482.6mm) 장착 레벨 사이에 고정하기 위한 용도
레벨 간격	500 - 750 mm
높이 단위	1 U

© Rittal 2025 2

특징

부하 용량(정적 하중)	150 N
적합한:	인클로저에 관계없이 다양하게 장착
참고 사항	Assembly parts should be ordered separately
포장 단위	1 개
관세 번호	73269098

© Rittal 2025 3