

Rittal – The System.

Faster – better – everywhere.



CX 6702.000

CX 콘솔 하부

상태: 2026. 7. 11 (원천: rittal.com/kr-ko)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6702.000 - CX 콘솔 하부

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



특징

주문 번호	CX 6702.000
버전	콘솔 하부
재료	인클로저: 강판 1.5mm 도어: 2.0 mm의 강판, 둘레 전체에 발포 PU 실링 처리 장착 플레이트: 강판, 2.5 mm
표면 처리	인클로저 및 도어: 전착도장, 외부 분체 코팅, 텍스처 도장 장착 플레이트: 아연도금
색상	RAL 7035
제공 범위	인클로저 위쪽 개방 전면 도어 또는 이중 도어, 3포인트 잠금 시스템 포함 장착 플레이트 글랜드 플레이트 잠금장치: 3mm 이중 걸림

특징

치수	폭: 1,200 mm 높이: 675 mm 깊이: 400 mm
장착 플레이트 치수(폭 x 높이)	1,120 mm x 625 mm
도어 개수	2
도어 열림각	130°
IK 코드	IK10
참고 사항	콘솔 하부를 폐쇄하기 위한 트림 패널이 필요함 2분할형 콘솔 조립 시 콘솔 중앙부 및 콘솔 중앙부용 트림 패널이 필요함 3분할형 콘솔 조립 시 콘솔 중앙부 및 콘솔 상부가 필요함
IEC 60 529에 준하는 IP 보호 등급	IP 55
Protection category NEMA	NEMA 1 NEMA 12
기본 재료	강판
잠금 장치 개수	1
잠금장치 버전	3포인트 잠금 시스템
잠금장치 인서트	3mm 이중 걸림
잠금장치	잠금장치 버전: 3포인트 잠금 시스템 잠금 장치 개수: 1 잠금장치 인서트: 3mm 이중 걸림
포장 단위	1 개
순 중량	56 kg
총 무게	57.125 kg
관세 번호	94032080
ETIM 9	EC000784

특징

ETIM 8	EC000784
ECLASS 8.0	27180504
제품 설명	CX 콘솔 시스템, 콘솔 하부, WHD: 1200x675x400mm, 강판

승인

승인	UL + C-UL (listed)
설명	적합성 인증