



# Rittal – The System.

Faster – better – everywhere.



## SZ 2566.450

# Two-part gland plate with foam rubber cable clamp strip

Состояние: 07.05.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2566.450 - Two-part gland plate with foam rubber cable clamp strip для AX

The divided gland plate supports simple mounting on the enclosure and offers a range of different installation options. For simple insertion of cables with and without connectors into the enclosure. Special drilled holes in the gland plate ensure automatic potential equalisation during screw-fastening. Bolts, clips and earthing cables are no longer required.

## Функции

Арт. №	SZ 2566.450
Исполнение	two-piece
Материал	Листовая сталь
Цвет	RAL 7035
Комплект поставки	Вкл. крепежный материал
Указание	Соответствие размеров фланш-панелей можно найти у соответствующих корпусов. When installing in enclosure width >760 mm, 2 packs are required
Размер	Ширина: 401 мм Глубина: 221 мм
Подходит для	Тип корпуса: AX
Подходит для арт. №	1110.000 1114.000 1130.000 1213.000 1350.000 1115.000 1214.000
Фланш-панель	Размер: 6
Упаковка	1 шт.
Вес нетто	1,3 kg
Gross weight	1,36 kg

## Функции

PCF per pack (cradle-to-gate)	5,2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Код ТНВЭД	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Описание продукта	SZ Metal gland plate, two-part, for AX, with foam rubber cable clamp strip, WD 401x221 mm, for gland plate size 6