

Rittal – The System.

Faster – better – everywhere.



SZ 4000.058

Attachable sloped roof

Состояние: 17.06.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4000.058 - Attachable sloped roof для VX

For retrofitting individual or bayed VX25 enclosures made from spray-finished sheet steel, with the maximum possible opening to the adjacent roof at the baying point.



Функции

Арт. №	SZ 4000.058
Технические характеристики	Roof projection, front: 8 mm
Материал	Листовая сталь
Поверхность	Порошковое покрытие
Цвет	RAL 7035
Комплект поставки	Вкл. крепежный материал и уплотнения
Размер	Высота спереди: 35 мм
Степень защиты IP согл. МЭК 60529	IP 55
Protection category NEMA	NEMA 12
Указание к арт. №	При запросе или заказа просьба указывать полный индекс исполнения. Срок поставки по запросу

Функции

Design code number	Roof tilt: 1 = 30° (EHEDG standard) or 2 = 45° Enclosure width: ... mm (max. 1200 mm) Enclosure depth: ... mm 1 = for VX free-standing enclosure 2 = for bayed VX end enclosure, left (with T-section seal and connection accessories) 3 = for bayed VX end enclosure, right (with T-section seal and connection accessories) 4 = for bayed VX enclosure, centre (with T-section seal and connection accessories) Example: 1 - 800 - 600 - 1 (sloped attachment with 30° roof pitch - width 800 mm - depth 600 mm - for VX free-standing enclosure)
Упаковка	1 шт.
Вес нетто	2 kg
Gross weight	2,1 kg
Код ТНВЭД	94039910
