

Rittal – The System.

Faster – better – everywhere.



IT 5302.042

482.6 mm (19") cable link, depth-variable

Состояние: 25.06.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 5302.042 - 482.6 mm (19") cable link, depth-variable

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

Функции

Арт. №	IT 5302.042
Преимущества	<p>Cable entry at the front via brush strip for thermal partitioning of the cable entry zone</p> <p>Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear</p> <p>Fully depth-variable with versatile, infinitely adjustable extension of the cable link</p> <p>Prevents incorrect airflow by partitioning the transition</p> <p>Open at the top for easy retrofitting, even with cables already inserted</p> <p>Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip</p>
Материал	<p>Листовая сталь</p> <p>Щеточный буртик: пластик, UL 94-V0</p>
Поверхность	Окрашенная
Цвет	RAL 9005
Комплект поставки	<p>Cable link</p> <p>Щеточный буртик</p>
Возможности монтажа	Для крепления между передней и задней 19" монтажной плоскостью
Расстояние между плоскостями	500 - 750 мм
Единиц высоты	1 U
Нагрузочная способность (статическая)	150 N
Подходит для	для свободной установки
Указание	Assembly parts should be ordered separately

Функции

Упаковка	1 шт.
Вес нетто	6,8 kg
Gross weight	7,239 kg
PCF per pack (cradle-to-gate)	PCF-Wert 18,78 kg Co ² e
Код ТНВЭД	73269098
Описание продукта	19" cable bridge, depth-variable, 500 - 750 mm, RAL 9005