


Rittal – The System.

Faster – better – everywhere.



VX_IT 5302.168

Поперечная траверса

Состояние: 23.05.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX_IT 5302.168 - Поперечная траверса для 19" профильных шин VX IT

For depth- and width-variable mounting of dynamic 482.6 mm (19") mounting angles in the bottom of 800 mm wide VX IT network/server enclosures.

Функции

Арт. №	VX IT 5302.168
Исполнение	для 19" профильной шины VX IT dynamic
Описание продукта	Для крепление дюймовой профильной шины standard с регулировкой по ширине сетевые шкафы/шкафы для серверов VX IT шириной 800 мм.
Преимущества	Возможен симметричный или асимметричный монтаж Больше пространства для ввода кабеля или интеграции Liquid Cooling Unit (LCU) при односторонней, асимметричной (со смещением вбок) установке Оптимально для интеграции дюймовых профильных шин для альтернативного монтажа компонентов 21", 23" или 24" Для повышения энергоэффективности контроля микроклимата стойки, пространство по периметру дюймовой крепежной плоскости может закрываться воздуховодными панелями, что позволяет целенаправленно использовать поток охлаждающего воздуха и предотвращать смешивание
Материал	Листовая сталь
Поверхность	Окрашенная
Цвет	RAL 9005
Комплект поставки	Вкл. крепежный материал
Нагрузочная способность	The maximum load capacity of one mounting level on this cross-member is 7,500 N per mounting level or 15,000 N per enclosure.

Функции

Указание по монтажу	<p>It is attached directly onto the enclosure frame. Only for use on the underside of the mounting angles.</p> <p>On the top, cross members are added for the VX IT standard mounting angle 5302167. For screw-fastening the mounting angles to the cross members, a mounting bracket for VX IT 482.6 mm (19") mounting angles 5302169 is additionally required.</p>
Подходит для	Тип корпуса: VX IT Ширина: = 800 мм
Упаковка	2 шт.
Вес нетто	6,1 kg
Gross weight	6,3 kg
PCF per pack (cradle-to-gate)	13,3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Код ТНВЭД	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Описание продукта	VX IT cross-member for 19" mounting angles, dynamic, for depth- and width-variable mounting of 482.6 mm (19") mounting angles, dynamic, in the bottom of 800 mm wide VX IT network/server enclosures.