

Rittal – The System.

Faster – better – everywhere.



VX 5315.185

Compartment Rack VX IT

Состояние: 25.02.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5315.185 - Compartment Rack VX IT 4-секционная, с вентиляцией

VX IT, с вентиляцией, для системы контроля микроклимата помещения. 19" монтаж с 19" профильными шинами, с регулировкой по глубине, нагрузочная способность до 1500 кг в различных типоразмерах.



Функции

| | |
|----------------------------|---|
| Арт. № | VX 5315.185 |
| Преимущества | <p>Enclosure pre-configured with 482.6 mm (19") mounting angles at the front and rear of each compartment, adjustable individually and independently of each other</p> <p>Pre-configured 740 mm distance between mounting angles, individually adjustable</p> <p>Door hinges can be swapped from right to left</p> <p>Baying supported on all sides</p> <p>Air baffle plates integrated into the 19" mounting frame</p> <p>Max. door opening angle 130°, max. 115° in bayed suite</p> |
| Технические характеристики | Max. load capacity 250 kg per compartment |
| Материал | <p>Каркас шкафа: листовая сталь 1,5 мм</p> <p>Roof plate: Sheet steel, 1.5 mm</p> <p>Gland plate: Sheet steel, 1.0 mm</p> <p>Front and rear door: Sheet steel, 1.5 mm</p> <p>Mounting angles: Sheet steel, 2.5 mm</p> |
| General colour | RAL 7035 |

Функции

| | |
|--|--|
| Цвет | Рама корпуса и плоские детали: RAL 7035 19" mounting angles, hinges and handles spray-finished in RAL 9005 |
| Комплект поставки | VX IT compartment rack, with four independent installation compartments Each compartment with 482.6 mm (19") mounting angles, front and rear, screwed to the integrated dividers on the left and right Gland plate divided in the centre, pre-configured across the entire rack depth 4 sheet steel doors, vented, front and rear Контрольная ручка под профильный полуцилиндр 3524 E Including potential equalisation, prepared for the attachment of earthing straps Two 482.6 mm (19") mounting angles front and rear per compartment, depth-variable, front angles with all-round integrated air baffles 8 keys |
| Размер | Ширина: 600 мм Высота: 2.200 мм Глубина: 1.200 мм |
| Расстояние между плоскостями (в состоянии поставки) | 740 мм |
| Number front doors | 4 |
| Number back doors | 4 |
| 19" крепление | 4 x 11 U Incl. 482.6 mm (19") mounting angles front and rear per compartment, adjustable individually and independently of each other |
| Исполнение | Compartment Rack, 4 x 11 U |
| Roof design | One-piece roof plate, with cable entry on both sides in the centre part of the roof |
| Design doors | Door opening angle max. 130° Incl. 2-point locking rod |
| Rear door design | 4-секционная, с вентиляцией |
| Front door design | 4-секционная, с вентиляцией |

Функции

| | |
|---------------------------------------|--|
| Mounting angle design | 19" mounting angles in the VX IT Compartment Rack |
| Base design | Base frame with pull-out, two-part solid gland plate pre-assembled |
| Исполнение 19" плоскости (плоскостей) | 19" плоскость спереди и сзади 19" mounting level with universal mounting angles front and rear, depth-variable, 12.5 mm pitch pattern, screwed to the divider panels on the left and right, with integrated air baffle plates |
| Mounting angles position | 19" плоскость спереди и сзади |
| Указание | В зависимости от типа и места установки угол открытия двери может отличаться для конкретного случая |
| Основной материал | Листовая сталь |
| Упаковка | 1 шт. |
| Код ТНВЭД | 94032080 |
| ETIM 9 | EC002499 |
| ECLASS 8.0 | 27180207 |
| Описание продукта | VX IT Compartment Rack, vented, 4 compartments, 19" mounting angles front and rear, 4 x 11 U, WHD: 600x2200x1000 mm, enclosure frame and panel parts: RAL 7035, interior components: RAL 9005 |

Одобрения

| | |
|-------------|---|
| Сертификаты | Поверхность |
| Объяснения | Декларация производителя Декларация о соответствии |