

Rittal – The System.

Faster – better – everywhere.



IT 7100.110 OCP ORV3 rack

Состояние: 08.04.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 7100.110 - OCP ORV3 rack

Open. Efficient. Scalable. Your IT infrastructure from Rittal with OCP ORV3, without busbar. The Open Compute Project (OCP) brings together leading companies with the goal of making open IT infrastructures more efficient, scalable and sustainable. Rittal is supporting this vision with its OCP-compliant Open Rack Version 3 (ORV3), which is now also available without an integral busbar.



Функции

Арт. №	IT 7100.110
Исполнение	Open frame without busbar
Преимущества	Модульная система для индивидуальной возможности расширения Flexible busbar selection, to suit the rack power density Can be retrofitted without replacing the entire system Modular configuration for AI and HPC applications Hot-pluggable components in the rack simplify maintenance work May be supplemented with a suitable direct liquid cooling solution Quick integration thanks to integral castor modules, air baffle plates and levelling feet Our range of accessories includes IT and power rails, 482.6 mm (19") adaptors, doors and side panels
Материал	Листовая сталь
Поверхность	Грунтовка, снаружи порошковое покрытие
Цвет	RAL 9005

Функции

Комплект поставки	ОСР ORV3 rack 2 bracing struts, pre-assembled Установленные ролики для высокой нагрузки Levelling feet, pre-assembled Уплотнение для соединения в линейку
Размер	Ширина: 600 мм Высота: 2.286 мм Глубина: 1.068 мм
Единиц высоты	44 OU
Нагрузочная способность	14 000 N
Основной материал	Листовая сталь
Упаковка	1 шт.
Код ТНВЭД	94032080
ETIM 8	EC002499
ECLASS 8.0	27180207
Описание продукта	ОСР ORV3 rack without busbar, 44 OU, WHD: 600 x 2286 x 1068 mm, RAL 9005