

Rittal – The System.

Faster – better – everywhere.



VX 8100.780

Регулировочные ножки

Состояние: 02.04.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8100.780 - Регулировочные ножки для VX, TS, VX SE из нержавеющей стали

For direct mounting on the corner of the enclosure section frame. Also suitable for mounting on the VX base/plinth system. A base/plinth adaptor is required for mounting on the VX base/plinth system.

Функции

Арт. №	VX 8100.780
Материал	Нержавеющая сталь 1.4301 (AISI 304)
Указание	При монтаже на цоколь VX необходим цокольный адаптер
Макс. нагрузка (статическая) на элемент	3 000 Н
Размер	Резьба: M12
Подходит для	Тип корпуса: VX TS VX SE PC Система цоколей VX
Диапазон регулировки	30 - 110 мм
Упаковка	4 шт.
Вес нетто	0,8 kg
Gross weight	0,862 kg
Код ТНВЭД	73181900
ETIM 9	EC000721
ECLASS 8.0	27182003
Описание продукта	VX регулировочная ножка, нержавеющая сталь, с резьбой M12