

Rittal – The System.

Faster – better – everywhere.



VX 8100.780

Регулировочные ножки

Состояние: 22.05.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8100.780 - Регулировочные ножки для VX, TS, VX SE из нержавеющей стали

For direct mounting on the corner of the enclosure section frame. Also suitable for mounting on the VX base/plinth system. A base/plinth adaptor is required for mounting on the VX base/plinth system.

Функции

| | |
|---|--|
| Арт. № | VX 8100.780 |
| Материал | Нержавеющая сталь 1.4301 (AISI 304) |
| Указание | При монтаже на цоколь VX необходим цокольный адаптер |
| Макс. нагрузка (статическая) на элемент | 3 000 Н |
| Размер | Резьба: M12 |
| Подходит для | Тип корпуса: VX TS VX SE PC Система цоколей VX |
| Диапазон регулировки | 30 - 110 мм |
| Упаковка | 4 шт. |
| Вес нетто | 0,8 kg |
| Gross weight | 0,862 kg |
| Код ТНВЭД | 73181900 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Описание продукта | VX регулировочная ножка, нержавеющая сталь, с резьбой M12 |