

Rittal – The System.

Faster – better – everywhere.



RX 9360.000

RiLineX baying set

Состояние: 10.06.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the 3-pole complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.



Функции

Арт. №	RX 9360.000
Преимущества	Time savings thanks to fully digital product data Reduced assembly time thanks to pre-assembled complete board Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Tested and certified to IEC and UL Simple extension and baying
Материал	Upper part: Sheet steel, zinc-plated Contact plate: E-Cu, tin-plated Front cover: Polyamide (PA 6) Негорючесть согласно UL 94
Цвет	RAL 35745
Комплект поставки	3 busbar connectors 1 front cover 1 insulating plate
Степень защиты IP согл. МЭК 60 529	IP 2XB
Стандарты	МЭК 60 297-1/-2 UL 508

Функции

Номинальный ток макс.	780 A
Номинальный ток (UL)	780 A
Electrical ratings UL (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Номинальное импульсное напряжение U _{imp}	12 кВ
Rated voltage	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Номинальное напряжение изоляции U _i	1 000 V AC 1 500 V DC
Rated impulse withstand current	103 kA 115,5 kA
Rated short-term withstand current/t	45 kA/200 ms 52,5 kA/500 ms
Категория перенапряжения	4
Степень загрязнения	3
Количество полюсов	3-пол.
Подходит для арт. №	9360004 9360008 9360024 9360028 9360064 9360068 9360084 9360088
Fundamental frequency	50...60 Гц
Влажность воздуха (без конденсата)	10...90 %
Подходит для шин	30 x 5/10

Функции

Диапазон рабочих температур	-5 °C...55 °C
Размер	Ширина: 154 мм Высота: 240 мм Глубина: 77 мм
Упаковка	1 шт.
Вес нетто	1,88 kg
Gross weight	1,924 kg
Доля меди (кг / штук)	0,297
PCF per pack (cradle-to-gate)	10,32
Код ТНВЭД	85369010
ETIM 9	EC002270
Описание продукта	RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple, no-drill baying of boards between two bayed enclosures. Baying connectors are included with the supply.

Одобрения

Одобрения	UL + C-UL (listed)
Объяснения	Декларация о соответствии PCF-declaration