

Rittal – The System.

Faster – better – everywhere.



RX 9360.603

RiLineX CB component adaptor

Состояние: 13.05.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.603 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the top.



Функции

Арт. №	RX 9360.603
Исполнение	universal
Преимущества	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Материал	Полиамид (PA 6) Негорючесть согласно UL 94
Цвет	RAL 9005 RAL 35745
Степень защиты IP согл. МЭК 60 529	IP 2XB
Номинальное импульсное напряжение U_{imp}	8 кВ

Функции

Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Номинальное напряжение изоляции U_i	1 000 В
Степень загрязнения	3
Количество полюсов	3-пол.
Отвод проводов	сверху
Сечение	9 мм ² 6 мм ²
Подходит для производителя (тип)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Подходит для шинной системы	RiLineX RiLine60
Fundamental frequency	50...60 Гц
Влажность воздуха (без конденсата)	10...90 %
Подходит для шин	15 x 5/10 20 x 5/10 30 x 5/10
Диапазон рабочих температур	-25 °C...55 °C
Диапазон температур хранения	-25 °C...75 °C
Размер	Ширина: 81,9 мм Высота: 251,4 мм Глубина: 50,8 мм
Упаковка	1 шт.
Вес нетто	1,21 kg
Gross weight	1,217 kg
Доля меди (кг / штук)	0,375
Код ТНВЭД	39269097

Функции

Описание продукта

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the top.

Одобрения

Одобрения

UL + C-UL (listed)

Объяснения

Декларация о соответствии
PCF-declaration