

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.232

# Current measurement module

Состояние: 07.05.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.232 - Current measurement module

To extend the modular network analyser REM 801 with 8 additional current measurement channels.

## Функции

Арт. №	SV 9393.232
Исполнение	REM 800-CT-8-LP null
Диапазон рабочих температур	-10 °C...55 °C
Диапазон температур хранения	-25 °C...70 °C
Влажность воздуха (без конденсата)	5...95 %
Степень защиты IP согл. МЭК 60529	IP 20
For mounting on support rails	да
Current measurement inputs	8 (2x4) 2 systems – L1, L2, L3, N Individual channels
Measurement by way of low-power current transformer (secondary voltage)	0...0,4 В
Fundamental frequency	40...70 Гц
Harmonic	1...15
Упаковка	1 шт.
Вес нетто	0,29 kg
Gross weight	0,295 kg
Код ТНВЭД	85389099
Описание продукта	SV Current measurement module REM 800-CT-8-LP for secondary current converters

# Одобрения

---

Обяснения

Декларация о соответствии