

# Rittal – The System.

Faster – better – everywhere.



## AE 1339.500

## Compact enclosures AE

State: 2026.5.7 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# AE 1339.500 - Compact enclosures AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

## Features

|                                      |                                                                                                                                               |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                            | AE 1339.500                                                                                                                                   |
| Material                             | Enclosure: Sheet steel<br>Door: Sheet steel, all-round foamed-in PU seal                                                                      |
| Surface finish                       | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated                               |
| Colour                               | RAL 7035                                                                                                                                      |
| Supply includes                      | Enclosure with hinged door(s), of all-round solid construction<br>Gland plate(s) in enclosure base<br>Mounting plate<br>Lock: 3 mm double-bit |
| Protection category NEMA             | NEMA 4                                                                                                                                        |
| Protection category to IEC 60 529    | IP 66                                                                                                                                         |
| IK Code                              | IK08                                                                                                                                          |
| Dimensions                           | Width: 600 mm<br>Height: 380 mm<br>Depth: 350 mm                                                                                              |
| Material thickness - door            | 1.5 mm                                                                                                                                        |
| Material thickness - enclosure       | 1.5 mm                                                                                                                                        |
| Material thickness of mounting plate | 2.5 mm                                                                                                                                        |
| Dimensions mounting plate (W x H)    | 549 mm x 355 mm                                                                                                                               |
| Number of doors                      | 1                                                                                                                                             |
| Interchangeable door hinge           | Yes                                                                                                                                           |
| Number of locks                      | 1                                                                                                                                             |

# Features

---

|                       |                                                                                                             |
|-----------------------|-------------------------------------------------------------------------------------------------------------|
| Lock                  | Lock version: Cam<br>Number of locks: 1<br>Lock insert: 3 mm double-bit                                     |
| Gland plate           | Size: 5<br>Qty.: 1                                                                                          |
| Basic material        | Sheet steel                                                                                                 |
| Packs of              | 1 pc(s).                                                                                                    |
| Net weight            | 17.798 kg                                                                                                   |
| Gross weight          | 18.64 kg                                                                                                    |
| Customs tariff number | 94032080                                                                                                    |
| ECLASS 8.0            | 27180101                                                                                                    |
| Product description   | AE Compact enclosure, WHD: 600x380x350 mm, Sheet steel, with mounting plate, single-door, with one cam lock |

# Approvals

---

|              |                                                                               |
|--------------|-------------------------------------------------------------------------------|
| Approvals    | Bureau Veritas<br>DNV-GL<br>Lloyds Register of Shipping<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK                     |

# Tender text

Enclosure (compact enclosure),  
protection category IP 66

## Enclosure:

Robust steel sheet construction made from 1.25 mm or 1.5 mm steel sheet, folded and welded from a single piece, with protection channel around the door opening, rear panel with countersunk holes for wall mounting brackets. Enclosure base fitted with sheet steel gland plates.

## Doors:

1.5 mm - 2 mm sheet steel, flush-mounted, with foamed-in seal, vertical perforated mounting strips fitted on both sides, screw-fastened hinges. Hinges can be fitted on the left or right for single-door enclosures, 130° opening angle as per VDI (retrofitable to 180°), cam lock with double-bit insert as per DIN 43668

## Mounting plate:

2 - 3 mm sheet steel with system punchings, depth-adjustable stud mountings, zinc-plated.

## Accessories:

Lock inserts, wall mounting brackets, plastic gland plate, earthing straps, wiring plan pockets, door stay, viewing window, panels, heat exchangers, fan-and-filter units, heaters, swing frame, electronic accessories (for 600 mm wide enclosures only), rain canopy, 180° hinge

## Approvals:

UL, CSA, TÜV, Germanischer Lloyd, Lloyds Register of Shipping, Det Norske Veritas, USSR Register of Shipping

## Surface finish:

Panels cleaned, degreased, phosphated, electrophoretic

dipcoat primed and powder-coated with polyester powder  
in textured RAL 7035.

Dimensions (W x H x D): 600 x 380 x 350 mm