

# Rittal – The System.

Faster – better – everywhere.



## KL 1529.010 Terminal boxes KL

State: 2025.6.14 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KL 1529.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

## Features

Model No.	KL 1529.010
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Enclosure and cover: Brushed, grain 180
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 300 mm Height: 200 mm Depth: 120 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Lock	Number of locks: 4
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	2.7
Gross weight	2.975
Customs tariff number	84879090
EAN	4028177663343
E-Number Sweden	E3404380
ETIM 9	EC000261
ETIM 8	EC000261

# Features

---

ECLASS 8.0

27180101

# Approvals

---

Approvals

Bureau Veritas  
DNV-GL  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK