

Rittal – The System.

Faster – better – everywhere.



SR 2340.700

Swing frame, large, without trim panel

State: 2025.8.28 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 2340.700 - Swing frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, for mounting 482.6 mm (19") equipment.



Features

Model No.	SR 2340.700
Product description	For mounting 482.6 mm (19") equipment.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Cam with double-bit lock insert Parts for attaching to the installation kit
Assembly instruction	Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required
Note	For further installation options, see "Technical details"
To fit	Enclosure type: TS Width: = 600 mm = 1,200 mm Height: ≥ 2,000 mm
Units	40 U
To fit enclosure type	TS
Packs of	1 pc(s).
Net weight	12.271

Features

Gross weight	12.917
Customs tariff number	94039910
EAN	4028177021679
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261