
Rittal – The System.

Faster – better – everywhere.






AX 2363.010 Protective roof


State: 2025.12.10 (Source: rittal.com/lt-en)



AX 2363.010 - Protective roof for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above.







Features

| Model No. | AX 2363.010 |
|-----------------------|------------------------------------------------------------------------------------------------------------------|
| Product description | The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 240 |
| Supply includes | Assembly parts |
| Installation options | May also be screw-fastened for dynamic loads |
| Dimensions | Height: 43 mm |
| Type rating to UL 50E | Type 1 |
| | Type 3R |
| | Type 4 |
| | Type 4X |
| | Type 12 |
| To fit | Enclosure type: AX |
| | Width: = 1,000 mm |
| | Depth: = 300 mm |
| Packs of | 1 pc(s). |
| Net weight | 4.4 |

© Rittal 2025

Features

| Gross weight | 4.7 |
|-----------------------|---------------|
| Customs tariff number | 94039910 |
| EAN | 4028177938137 |
| E-Number Sweden | E3465323 |
| ETIM 9 | EC000744 |
| ETIM 8 | EC000744 |
| ECLASS 8.0 | 27182405 |

Approvals

Approvals UL + C-UL - FTTA