## Rittal – The System.

Faster – better – everywhere.





# SZ 2500.710 Socket box

State: 2025.10.31 (Source: rittal.com/lt-en)




## SZ 2500.710 - Socket box for LED system light

In combination with the LED system light, the socket box creates a flexible modular system for international use.







#### **Features**

Model No.	SZ 2500.710	
Product description	In combination with the LED system light, the socket box creates flexible modular system for international use.	
Benefits	Identical connection accessories as for LED system light Cascadable with LED system light Supports flexible installation throughout the entire enclosure and on the tubular door frame Ergonomic positioning of the socket box on surfaces No additional wiring required, thanks to simple connection technology and integration of the LED system light into the circuit	
Material	Plastic	
Colour	RAL 7016	
Supply includes	Assembly parts	
Connection options	Infeed, 3-pole Through-wiring, 3-pole	
Note	Depending on the application, through-wiring or a 3-pole infeed may be required	

© Rittal 2025

### Features

Dimensions	Width: 163 mm
	Height: 68 mm
	Depth: 43.5 mm
	·
Operating temperature range	-20 °C55 °C
Sockets	D, earthing-pin (type F, CEE 7/3)
Rated operating voltage	195 V - 250 V, 50 Hz/60 Hz
Packs of	1 pc(s).
Net weight	0.26
Gross weight	0.28
Customs tariff number	85366990
EAN	4028177956896
ETIM 9	EC000330
ETIM 8	EC000330
ECLASS 8.0	27142604

## **Approvals**

Explanations	Declaration of conformity	

© Rittal 2025 3