

Rittal – The System.

Faster – better – everywhere.



SZ 2561.100

Metal gland plate

State: 2026.5.23 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2561.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

| | |
|-----------------------------------|---|
| Model No. | SZ 2561.100 |
| Product description | Simply knock out the holes for the cable glands using a screwdriver. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 9 x M20 4 x M25 2 x M32 |
| Dimensions | Width: 330 mm Depth: 90 mm |
| To fit | Enclosure type: AE |
| Gland plate | Size: 3 |
| Protection category to IEC 60 529 | IP 66 when mounting in the usual position at the bottom |
| Packs of | 1 pc(s). |
| Net weight | 0.31 kg |
| Gross weight | 0.356 kg |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Metal gland plate, with metric knock-outs, WD: 330x90 mm, size: 3 |