
### Rittal - The System.

Faster – better – everywhere.





### SZ 2565.450

# Two-part gland plate with foam rubber cable clamp strip

State: 2025.10.24 (Source: rittal.com/lt-en)



## SZ 2565.450 - Two-part gland plate with foam rubber cable clamp strip for AX

The divided gland plate supports simple mounting on the enclosure and offers a range of different installation options. For simple insertion of cables with and without connectors into the enclosure. Special drilled holes in the gland plate ensure automatic potential equalisation during screw-fastening. Bolts, clips and earthing cables are no longer required.

#### **Features**

| Model No.        | SZ 2565.450  |
|------------------|--|
| Design           | two-piece  |
| Material         | Sheet steel  |
| Colour           | RAL 7035   |
| Supply includes  | Assembly parts   |
| Note             | The allocation of gland plate sizes is indicated on the relevant enclosures When installing in enclosure width >760 mm, 2 packs are required |
| Dimensions       | Width: 301 mm<br>Depth: 221 mm   |
| To fit           | Enclosure type: AX   |
| To fit Model No. | 1037.000<br>1055.000<br>1073.000<br>1180.000<br>1280.000<br>1338.000<br>1181.000<br>1281.000   |
| Gland plate      | Size: 5  |
| Packs of         | 1 pc(s).   |
| Net weight       | 0.95   |
| Gross weight     | 1.02   |
|                  |  |

© Rittal 2025

### **Features**

| PCF per pack (cradle-to-gate) | 3.9 kg CO2 eq (Cat B)  |
|-------------------------------|--|
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 73079100   |
| EAN                           | 4028177973152  |
| ETIM 9                        | EC000211   |
| ETIM 8                        | EC000211   |
| ECLASS 8.0                    | 27142421   |

© Rittal 2025 3