
Rittal – The System.

Faster – better – everywhere.



# SZ 2567.450

# Two-part gland plate with foam rubber cable clamp strip

State: 2026.10.31 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SZ 2567.450 - Two-part gland plate with foam rubber cable clamp strip for AX

The divided gland plate supports simple mounting on the enclosure and offers a range of different installation options. For simple insertion of cables with and without connectors into the enclosure. Special drilled holes in the gland plate ensure automatic potential equalisation during screw-fastening. Bolts, clips and earthing cables are no longer required.

## Features

| | |
|---|---|
| Model No. | SZ 2567.450 |
| Design | two-piece |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures<br>When installing in enclosure width >760 mm, 2 packs are required |
| Dimensions | Width: 436 mm<br>Depth: 221 mm |
| To fit | Enclosure type: AX |
| To fit Model No. | 1260.000<br>1339.000<br>1360.000<br>1376.000<br>1059.000<br>1091.000<br>1116.000<br>1261.000 |
| Gland plate | Size: 7 |
| Packs of | 1 pc(s). |
| Net weight | 1.4 kg |
| Gross weight | 1.46 kg |

© Rittal 2026

# Features

| | |
|---|---|
| PCF per pack (cradle-to-gate) | 5.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Metal gland plate, two-part, for AX, with foam rubber cable clamp strip, WD 436x221 mm, for gland plate size 7 |