


Rittal – The System.

Faster – better – everywhere.



SZ 2567.450

**Two-part gland plate with foam
rubber cable clamp strip**

State: 2025.5.3 (Source: rittal.com/lt-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2567.450 - Two-part gland plate with foam rubber cable clamp strip for AX

The divided gland plate supports simple mounting on the enclosure and offers a range of different installation options. For simple insertion of cables with and without connectors into the enclosure. Special drilled holes in the gland plate ensure automatic potential equalisation during screw-fastening. Bolts, clips and earthing cables are no longer required.

Features

| | |
|-------------------------------|---|
| Model No. | SZ 2567.450 |
| Design | two-piece |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures When installing in enclosure width >760 mm, 2 packs are required |
| Dimensions | Width: 436 mm Depth: 221 mm |
| To fit | Enclosure type: AX |
| To fit Model No. | 1260.000 1339.000 1360.000 1376.000 1059.000 1091.000 1116.000 1261.000 |
| Gland plate | Size: 7 |
| PCF per pack (cradle-to-gate) | 5.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 73269098 |
| EAN | 4028177973145 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |