

Rittal – The System.

Faster – better – everywhere.



AX 2584.100 Pole clamp

State: 2026.4.12 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2584.100 - Pole clamp for AX, KX, AX plastic, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.



Features

Model No.	AX 2584.100
Product description	For reliable, convenient fastening to round or square poles.
Technical specifications	For pole diameter: Ø from 40 to 170 mm For pole size: □ from 50 to 150 mm
Material	Mounting angles, clamping section: Sheet steel Clamping strap: Stainless steel 1.4301 (AISI 304)
Surface finish	Mounting angle, clamp strip: Galvanic zinc-nickel, passivated
Supply includes	2 mounting angles, 600 mm long 4 clamping sections 2 clamping straps 4 clamping brackets 4 self-tapping M10 bolts for mounting onto the enclosure
Note	Only suitable for enclosures up to a width of 600 mm.

Features

To fit	Enclosure type: AX KX AX plastic AX IT CS wall-mounted enclosures AX outdoor housing AE KL EB AX wall-mounted enclosure, 3-part
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 12
Packs of	2 pc(s).
Net weight	1.88 kg
Gross weight	1.96 kg
PCF per pack (cradle-to-gate)	7.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	83024900
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Product description	AX Pole clamp

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------