

Rittal – The System.

Faster – better – everywhere.



TP 2695.500

Universal consoles TP

State: 2026.1.30 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 2695.500 - Universal consoles TP

Universal consoles TP, high level of stability and protection category IP 55 because the body is more or less manufactured from a single piece. Flexible front design, optionally with drawers or desk section. Easy accessibility thanks to divided doors. Interchangeable lock insert.

Features

Model No.	TP 2695.500
Design	with tall front door
Product modification	The universal console comes with the new mounting plate of the baying enclosure system VX25.
Material	Enclosure, gland plates: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm Mounting plate: Sheet steel, 3.0 mm
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure with door(s) Mounting plate Gland plates
Dimensions	Width: 600 mm Height: 1,300 mm
Dimensions mounting plate (W x H)	499 mm x 1,196 mm
Depth (top)	417.5 mm
Depth (bottom)	500 mm
IK Code	IK08
Note	For universal console with short front door: The desk section should be fitted in order to maintain the protection category.
IP protection category to IEC 60529	IP 55

Features

Protection category NEMA	NEMA 12
Basic material	Sheet steel
Dimensions	Width: 600 mm Height: 1,300 mm Depth (top): 417.5 mm Depth (bottom): 500 mm
Packs of	1 pc(s).
Net weight	74.1
Gross weight	78
Customs tariff number	94032080
EAN	4028177031548
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	TÜV UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK