

# Rittal – The System.

Faster – better – everywhere.



## FT 2730.010 Viewing window

State: 2026.6.29 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2730.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.



## Features

Model No.	FT 2730.010
Design	30 section
Product description	For external mounting on AX enclosures instead of a door and on surfaces.
Material	Frame: Aluminium, natural anodised. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
To fit Model No.	1039.000 1339.000 1009.000
To fit	Enclosure type: AX Width: = 600 mm Height: = 380 mm
Dimensions	Width: 597 mm Height: 377 mm Depth: 36 mm
Visible area	Viewing window width: 537 mm Viewing window height: 317 mm

# Features

Build depth for components (max.)	32 mm
Visible area	Width: 537 mm Height: 317 mm
Packs of	1 pc(s).
Net weight	2.6 kg
Gross weight	2.72 kg
Customs tariff number	76101000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	FT Viewing window, WHD: 597x377x36 mm, for AX enclosures instead of the door and surfaces