

Rittal – The System.

Faster – better – everywhere.



FT 2784.000 Acrylic glazed cover

State: 2025.8.15 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2784.000 - Acrylic glazed cover

For the protection of display and control components in standard 482.6 mm (19") or metric sizes.

Features

| | |
|-----------------------------------|---|
| Model No. | FT 2784.000 |
| Design | Metric |
| Product description | With security lock, lock no. 3524 E. |
| Material | Frame: Extruded aluminium sections with die-cast corner pieces Glass panel: Smoked acrylic |
| Supply includes | Hinges and assembly parts. Lock insert no. 3524 E |
| Protection category to IEC 60 529 | IP 54 |
| Dimensions | Width: 400 mm Height: 200 mm Depth: 47.5 mm |
| Visible area | Viewing window width: 360 mm Viewing window height: 179.5 mm |
| Build depth for components (max.) | 43 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.3 |
| Gross weight | 1.4 |
| Customs tariff number | 39269097 |
| EAN | 4028177032279 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182301 |