

# Rittal – The System.

Faster – better – everywhere.



## FT 2793.560 Viewing window

Source: 2026.5.13 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2793.560 - Viewing window Stainless steel

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access. Made from stainless steel 1.4301 (AISI 304).



## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | FT 2793.560   |
| Product description               | Fitted as standard with internal 130° hinges and all-round seal.  |
| Material                          | Stainless steel 1.4301 (AISI 304)<br>Single-pane safety glass   |
| Supply includes                   | Assembly parts  |
| Protection category to IEC 60 529 | IP 54   |
| Note                              | Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm). |
| Dimensions                        | Width: 522 mm<br>Height: 600 mm<br>Depth: 38 mm   |
| Visible area                      | Viewing window width: 408 mm<br>Viewing window height: 543 mm   |
| Build depth for components (max.) | 31 mm   |

# Features

|                       |   |
|-----------------------|---|
| Packs of              | 1 pc(s).  |
| Net weight            | 6.175 kg  |
| Gross weight          | 6.5 kg  |
| Customs tariff number | 76101000  |
| ETIM 9                | EC002527  |
| ETIM 8                | EC002527  |
| ECLASS 8.0            | 27182204  |
| Product description   | FT Viewing window, WHD: 522x600x38 mm, Stainless steel 1.4301 |