

Rittal – The System.

Faster – better – everywhere.



FT 2793.560 Viewing window

Source: 2025.7.13 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2793.560 - Viewing window Stainless steel

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access. Made from stainless steel 1.4301 (AISI 304).



Features

Model No.	FT 2793.560
Product description	Fitted as standard with internal 130° hinges and all-round seal.
Material	Stainless steel 1.4301 (AISI 304) Single-pane safety glass
Supply includes	Assembly parts
Protection category to IEC 60 529	IP 54
Note	Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).
Dimensions	Width: 522 mm Height: 600 mm Depth: 38 mm
Visible area	Viewing window width: 408 mm Viewing window height: 543 mm
Build depth for components (max.)	31 mm

Features

Packs of	1 pc(s).
Net weight	6.175
Gross weight	6.5
Customs tariff number	76101000
EAN	4028177149656
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204