

Rittal – The System.

Faster – better – everywhere.



SO 2890.000 Levelling feet

State: 2026.4.5 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SO 2890.000 - Levelling feet for base/plinth TS, stainless steel and base/plinth, complete, stainless steel

For direct mounting underneath the TS base/plinth and the base/plinth, complete. For unhindered access e.g. when cleaning the floor, and to compensate for floor irregularities.

Features

| | |
|---|--|
| Model No. | SO 2890.000 |
| Product description | For direct mounting underneath the base/plinth TS and the base/plinth, complete. For unhindered access e.g. when cleaning the floor, and to compensate for floor irregularities. |
| Benefits | Unhindered access, e.g. for floor cleaning To compensate for height differences with floor irregularities |
| Material | Stainless steel 1.4301 (AISI 304) |
| Installation options | For direct mounting underneath the base/plinth TS and the base/plinth, complete |
| Max. load capacity (static) per component | 400 kg |
| Dimensions | Thread: M16 |
| Levelling range | 45 - 120 mm |
| Packs of | 4 pc(s). |
| Net weight | 2.4 kg |
| Gross weight | 2.74 kg |
| Customs tariff number | 73181900 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | SO Levelling foot, for TS, base/plinth complete, thread M16, stainless steel 1.4301 |