

# Rittal – The System.

Faster – better – everywhere.



## SK 3201.840

# Modular climate control concept – climate control door VX25

State: 2026.5.9 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3201.840 - Modular climate control concept – climate control door VX25 for installing cooling modules

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX.

## Features

Model No.	SK 3201.840
Product description	Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.
Material	Sheet steel
Colour	RAL 7035
Supply includes	Climate control door without preconfigured cooling module 180° hinges, door opening angle approx. 130°
Note on Model No.	To fit VX enclosures For 1200 mm wide VX enclosures, the existing hinged door may be used, irrespective of the device position (left or right) L/h door hinge
To fit	Unit positioned on the left
To fit	Enclosure type: VX: = 600 mm: = 1,800 mm Enclosure type: = 1,200 mm
Packs of	1 pc(s).
Net weight	25.7 kg
Gross weight	26.8 kg
Customs tariff number	94039910
ETIM 9	EC002510
ETIM 8	EC002510
ECLASS 8.0	27180702

# Features

---

Product description

SK climate control door for cooling module,, for VX25 600/1200 mm wide, 1800 mm high, door hinge left

# Approvals

---

Explanations

Declaration of conformity - F-gas regulation

# Tender text

SK 3201.840

Modular climate control concept – climate control door VX25 for installing cooling modules

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.

Material: Sheet steel

Colour: RAL 7035

To fit VX enclosures

Dimensions WxH [mm]: 600/1200x1800

door hinge left