

Rittal – The System.

Faster – better – everywhere.



SK 3322.700

Chopped-fibre filter mat

State: 2026.1.30 (Source: [ittal.com/lt-en](https://www.ittal.com/lt-en))



FRIEDHELM LOH GROUP

SK 3322.700 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3322.700
Design	for filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibres
Note	No suitable for use in EMC filter fans.
To fit Model No.	3238....
Dimensions	Width: 120 mm Height: 120 mm Depth: 11 mm
Filter class	to DIN EN 779: G2 to DIN EN ISO 16890: ISO Coarse 50%
Packs of	5 pc(s).
Net weight	0.01
Gross weight	0.013
Customs tariff number	56039390
EAN	4028177156159
E-Number Sweden	E3404736
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UR + C-UR (recognized)
Certificates	EAC