

Rittal – The System.

Faster – better – everywhere.



SK 3355.100 Guide frame

State: 2025.9.11 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3355.100 - Guide frame for Vario rack-mounted fan

Guide frame for Vario rack-mounted fan: Installation directly in the subrack or using two mounting brackets on the 482.6 mm (19") mounting angles.



Features

Model No.	SK 3355.100
Supply includes	Guide frame Connector and fitted connection cable Mounting bracket for optional attachment to the 482.6 mm (19") mounting level Assembly parts
Length of connection cable	3 m
To fit Model No.	3350.230 3351.230 3352.230
Electrical connection	115 V, 50/60 Hz 230 V, 50/60 Hz
Packs of	1 pc(s).
Net weight	0.88
Gross weight	0.905
Customs tariff number	84149000
EAN	4028177041677
ETIM 9	EC002513
ETIM 8	EC002513

Features

ECLASS 8.0

27180706