


Rittal – The System.

Faster – better – everywhere.



AS 4050.200 Assembly frame

State: 2025.8.21 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.200 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.

Features

Model No.	AS 4050.200
Design	200 EN (electrically tilt-adjustable)
Product description	The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.
Benefits	For ergonomic, back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimum space requirements during non-use Simple handling due to four castors including total lock function Variable mounting plate attachment with a quick-release fastener
Technical specifications	Tilt adjustment approx. 0 – 80°
Supply includes	Assembly frame 1 clamping unit pack, bottom 1 clamping unit pack, top Charger unit Battery
Note	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.
Machine dimensions	Width: 1,400 mm Depth: 1,250 mm
Dimensions support surface max.	Width: 1,110 mm Height: 1,900 mm
Dimensions support surface min.	Width: 1,110 mm Height: 1,230 mm
Load capacity	200 kg

Features

Working height	Working height (min.): 90 cm Working height (max.): 90 cm
Packs of	1 pc(s).
Net weight	130
Gross weight	148
Customs tariff number	84279000
EAN	4028177804616
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	36659090

Approvals

Explanations	Declaration of conformity
--------------	---------------------------