

Rittal – The System.

Faster – better – everywhere.



AS 4050.450 Cutting machine C8

State: 2025.7.19 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.450 - Cutting machine C8

Semi-automated machine for cutting wires to an individually adjustable size.

Features

Model No.	AS 4050.450
Design	With command panel
Product description	Semi-automated machine for cutting wires to an individually adjustable length.
Benefits	Easy to operate Simple insertion of the wires Simple opening of the feed rollers PC compatible
Technical specifications	Fine-wire strand 0.08 - 10 mm ² (AWG 28 - 8) Single-wire strand 0.08 - 2.5 mm ² (AWG 28 - 14) For wire lengths 1 - 99999 mm Feed rate 0 - 1.5 m/s Controllable pressing force of the feed rollers DC servo-drive
Supply includes	Cutting machine C8 Software on CD-ROM Connection cable with connector
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	120 VA
Machine dimensions	Width: 380 mm Height: 470 mm Depth: 360 mm
Packs of	1 pc(s).
Net weight	24
Gross weight	24
Customs tariff number	84798997
EAN	4028177804845

Features

ECLASS 8.0

36600890