

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.740 Wire end ferrules

State: 2026.5.10 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.740 - Wire end ferrules loose

With plastic collar.



## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4050.740   |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene  |
| Colour                   | Black   |
| Length                   | 12 mm   |
| AWG                      | 16  |
| Internal diameter        | 3.5 mm  |
| For cross-section        | 1.5 mm <sup>2</sup>   |
| DIN colour code          | Yes   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines.<br>For bespoke advice, please contact your Rittal sales consultant. |
| Standards                | AEH DIN 46228   |
| To fit Model No.         | 4051.205<br>4051.210  |
| Delivery form            | Loose (10 packs of 100)   |
| Packs of                 | 1,000 pc(s).  |

# Features

---

|                       |  |
|-----------------------|--|
| Net weight            | 1 kg   |
| Customs tariff number | 85369010   |
| ETIM 9                | EC000005   |
| ETIM 8                | EC000005   |
| ECLASS 8.0            | 36659290   |
| Product description   | Wire end ferrules for wire processing, 1.5 mm <sup>2</sup> , black, loose, 12 mm, 10x100 |

# Approvals

---

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|