
Rittal – The System.

Faster – better – everywhere.



AS 4050.766
Wire end ferrules

State: 2026.11.1 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4050.766 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4050.766
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	10 mm
AWG	18
Internal diameter	2.8 mm
Rittal colour code	Yes
For cross-section	0.75 mm²
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
To fit Model No.	4051.205 4051.210 4050.452
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5 kg
Gross weight	0.049 kg
Customs tariff number	85369010
ETIM 9	EC000005

© Rittal 2026

Features

ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules for wire processing, 0.75 mm², AWG 18, 10 mm, white, loose, 500 pcs.

Approvals

Approvals	UL + C-UL (listed) UR