
Rittal – The System.

Faster - better - everywhere.





AS 4050.773 Wire end ferrules

State: 2025.12.8 (Source: rittal.com/lt-en)



AS 4050.773 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4050.773	
Product description	With plastic collar.	
Technical specifications	Heat-resistant to 105 °C	
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene	
Colour	Red	
Length	8 mm	
AWG	16	
Internal diameter	3.5 mm	
Rittal colour code	Yes	
For cross-section	1.5 mm²	
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.	
Standards	AEH DIN 46228	
To fit Model No.	4051.205 4051.210 4050.452	
Delivery form	Loose	
Packs of	500 pc(s).	
Net weight	0.5	
Gross weight	0.058	
Customs tariff number	85369010	
EAN	4028177815728	

© Rittal 2025

Features

ETIM 9	EC000005	
ETIM 8	EC000005	
ECLASS 8.0	36659290	

Approvals

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3