Rittal – The System.

Faster – better – everywhere.



AS 4050.783
Wire end ferrules

State: 2026.10.30 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4050.783 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4050.783
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Grey
Length	12 mm
AWG	12
Internal diameter	4.8 mm
For cross-section	4 mm²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
To fit Model No.	4051.210
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5 kg
Gross weight	0.5 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2026

Features

ECLASS 8.0	36659290
Product description	Wire end ferrules for wire processing, 4 mm², AWG 12, grey, 12 mm, loose, 500 pcs.

Approvals

Approvals	UL + C-UL (listed) UR