

Rittal – The System.

Faster – better – everywhere.



AS 4051.539 Wire end ferrules

State: 2025.7.10 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.539 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.539
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Red
To fit	Enclosure type: Crimping machine RC
Length	10 mm
AWG	16
Internal diameter	4 mm
Rittal colour code	Yes
For cross-section	1.5 mm ²
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	4,000 pc(s).
Net weight	4
Gross weight	0.704
Customs tariff number	85369010
EAN	4028177937871
ETIM 9	EC000005
ETIM 8	EC000005

Features

ECLASS 8.0	36659290
------------	----------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------