
### Rittal – The System.

Faster – better – everywhere.





# AS 4051.544 Wire end ferrules

State: 2025.10.29 (Source: rittal.com/lt-en)



#### AS 4051.544 - Wire end ferrules on a reel

With plastic collar.

#### **Features**

Model No.	AS 4051.544
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	10 mm
AWG	20
Internal diameter	2.9 mm
For cross-section	0.5 mm²
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	4,000 pc(s).
Net weight	4
Customs tariff number	85369010
EAN	4028177937925
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2025

## Approvals

Approvals

UL + C-UL (listed)

© Rittal 2025 3