

Rittal – The System.

Faster – better – everywhere.



AS 4052.107 Screwdrivers

State: 2026.6.12 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.107 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

| | |
|---------------------------|--|
| Model No. | AS 4052.107 |
| Design | Isolation protection 1000 V for slot-head screws |
| Product description | With a long, slender handle and high-performance tip with non-transfer insulation. |
| Benefits | Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working |
| Material | Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic |
| Colour | Handle: Anthracite and Rittal Power Pink |
| Blade dia. | 6.5 mm |
| Blade length | 125 mm |
| Blade (width x thickness) | 6.5 x 1.2 mm |
| Blade tip | SL |
| Handle dia. | 27 mm |
| Handle length | 115 mm |
| Standards | IEC 60 900 |
| Packs of | 3 pc(s). |
| Customs tariff number | 82054000 |
| ETIM 9 | EC000144 |

Features

| | |
|---------------------|------------------------------------|
| ETIM 8 | EC000158 |
| ECLASS 8.0 | 21040406 |
| Product description | Screwdriver insulated SL 6,5 x 1,2 |
