

# Rittal – The System.

Faster – better – everywhere.



## SZ 4127.010 Door-operated switch

State: 2025.9.18 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4127.010 - Door-operated switch

with mounting accessories, with or without connection cable.

## Features

|   |  |
|---|--|
| Model No.                                       | SZ 4127.010  |
| Design  | Without connection cable   |
| Note  | For installation in VX IT only in conjunction with VX mounting bracket for door-operated switch  |
| Rated impulse withstand voltage, phase to phase | 6000 V AC  |
| Rated insulation voltage                        | 400 V AC   |
| Installation options                            | for LED system light<br>for standard and courtesy light without integral door-operated switch<br>for cooling units and air-water heat exchangers |
| Electrical connection                           | 240 V AC/6 A<br>125 V AC/8 A<br>24 V AC/6 A<br>24 V DC/6 A   |
| Rated operating voltage                         | 400 V  |
| IP protection category to IEC 60529             | IP 40  |
| Packs of  | 1 pc(s).   |
| Net weight                                      | 0.068  |
| Gross weight                                    | 0.076  |
| Customs tariff number                           | 85365019   |
| EAN   | 4028177497740  |
| E-Number Sweden                                 | E3404494   |
| ETIM 9  | EC002626   |
| ETIM 8  | EC002626   |

# Features

---

ECLASS 8.0

27189266

# Approvals

---

Approvals

CQC  
CQC-CCC  
CSA  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK