

# Rittal – The System.

Faster – better – everywhere.



## SZ 4315.320

### Door-operated switch

State: 2025.12.18 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4315.320 - Door-operated switch

with mounting accessories, with or without connection cable.

## Features

Model No.	SZ 4315.320
Design	With connection cable
Length	1,000 mm
Rated impulse withstand voltage, phase to phase	6000 V AC
Rated insulation voltage	400 V AC
Installation options	for standard and courtesy light without integral door-operated switch
Dimensions	Length: 1,000 mm
Electrical connection	240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A
Rated operating voltage	400 V
IP protection category to IEC 60529	IP 40
Packs of	1 pc(s).
Net weight	0.139
Gross weight	0.149
Customs tariff number	85365019
EAN	4028177581333
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266

# Approvals

---

Approvals

CQC  
CQC-CCC

---

Explanations

Declaration of conformity  
Declaration of conformity UK