
Rittal – The System.

Faster – better – everywhere.



VX 5301.332

Gland plate module, one-piece, with brush strip

State: 2026.10.30 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 5301.332 - Gland plate module, one-piece, with brush strip for VX IT

For targeted cable entry from below.

Features

Model No.	VX 5301.332
Design	one-piece, with brush strip
Product description	For targeted cable entry from below.
Material	Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free
Surface finish	Module plate: Zinc-plated
Supply includes	Assembly parts
Assembly instruction	Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm.
Note	Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529
Dimensions	Depth: 237.5 mm
To fit	Enclosure type: VX IT Width: = 600 mm
Packs of	1 pc(s).
Net weight	1.14 kg
Gross weight	1.34 kg
PCF per pack (cradle-to-gate)	5.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002620

© Rittal 2026

Features

ECLASS 8.0	27189261
Product description	VX IT gland plate module with brush strip, for width 600 mm, W x D 600 x 237.5 mm, one-piece, sheet steel

Tender text

VX IT Gland plate module, Art.-No. 5301.332,
with brush strip, for cable routing
For a rack width of 600 mm
Depth: 237,5 mm
For VX, VX IT
For a cable entry over brushes
Module plate: Sheet steel, zinc-plated
Brush strip: UL 94-HB, halogen-free

© Rittal 2026