
### Rittal – The System.

Faster – better – everywhere.





DK 5502.265

# Cable management panel with brush strip

State: 2025.11.4 (Source: rittal.com/lt-en)



## DK 5502.265 - Cable management panel with brush strip 482.6 mm (19")

With cut-out 390 x 40 mm (2 U) or 390 x 20 mm (1 U) with brush insert, accommodation facility for cable clamp straps.







#### **Features**

Model No.	DK 5502.265
Product description	For convenient, simple cable routing between two areas separated by a 482.6 mm (19") mounting level, for example, between the front and rear areas of the 482.6 mm (19") mounting level.
Applications	For locking and simultaneous cable routing in installation zones to the 1 U, 482.6 mm (19") mounting standard
Material	Sheet steel Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Colour	RAL 9005
Mounting cut-out	Width:390 mm Height:40 mm
Dimensions	Width: 482.6 mm
Units	2 U
Packs of	1 pc(s).
Net weight	0.7
Gross weight	0.703

© Rittal 2025

### **Features**

Customs tariff number	73269098
EAN	4028177679375
E-Number Sweden	E7239793
ETIM 9	EC000322
ECLASS 8.0	27400604

© Rittal 2025 3