Rittal – The System.

Faster – better – everywhere.



DK 5502.550

Gland plate

State: 2026.10.31 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 5502.550 - Gland plate for TS IT, TX CableNet

Potential equalisation is provided via assembly components and earthing points. The gland plate set is used to conceal the entire base opening.

Features

Model No.	DK 5502.550
Design	Gland plate, solid, with sliding panel, multi-piece
Product description	Potential equalisation is provided via assembly components and earthing points. Gland plate set: To conceal the entire base opening. Gland plate modules: Select suitable modules depending on the application.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Note	To select the required module plates for completing the base area, please observe the information about the base mount included in the assembly instructions.
To fit	Enclosure type: TS IT TX CableNet Width: 800 mm Depth: 1,000 mm
Packs of	1 pc(s).
Net weight	7.94 kg
Gross weight	8.42 kg
PCF per pack (cradle-to-gate)	32.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261

Features

Product description	DK Gland plate set, solid gland plate, with sliding panel, multi-piece, WxD: 800x1000 mm, for TS IT, TX CableNet, sheet steel, zinc-plated

Tender text

DK Gland plate Set,
solid, multi-piece
WxD: 800x1000 mm,
for TS IT, TX CableNet
Sheet steel, zinc-plated

© Rittal 2026