

Rittal – The System.

Faster – better – everywhere.



CP 6206.480

Connection console VESA 75/100

State: 2026.2.8 (Source: [ittal.com/lt-en](https://www.ittal.com/lt-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

CP 6206.480 - Connection console VESA 75/100

For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75/100 connection. May be connected to Rittal support arm systems CP 40 and CP 60, and also CP 120 by using an adaptor from support arm connection Ø 130 mm to rectangular 120 x 65 mm.



Features

Model No.	CP 6206.480
Design	Connection to Rittal support arm systems
Product description	For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75 / 100 connection.
Benefits	<p>Fast, simple one-man assembly using machined keyholes</p> <p>More space for installation and servicing</p> <p>Cables may be routed to devices outside and below the console</p> <p>Removable cover for simple cable routing and access to interior device connections</p> <p>Integral cable clamping facilities</p> <p>Cover and captive screws</p>
Material	Die-cast zinc
Colour	Connection console: RAL 7035 Cover: RAL 7024
Supply includes	Seal and assembly parts Cable ties for cable clamping
Rifid y/n	Yes
Note	Depending on the application, an attachment, coupling or adaptor are required
Load capacity	800 N

Features

Packs of 1 pc(s).

Net weight 2.5

Gross weight 2.775

Customs tariff number 73269098

EAN 4028177693920

ETIM 9 EC002622

ECLASS 8.0 27189263

Approvals

Explanations

Manufacturer's declaration