

Rittal – The System.

Faster – better – everywhere.



SM 6450.050 Power pack

State: 2026.5.23 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 6450.050 - Power pack For TFT monitor

With IEC320 socket, with cable (1.5 m) for connecting to the TFT monitor.

Features

Model No.	SM 6450.050
Material	Enclosure: Plastic
Supply includes	Power supply unit with IEC 60 320 connector C14 Integral cable (1.5 m) for connecting to the TFT monitor
Dimensions	Width: 112 mm Height: 31 mm Depth: 47 mm
Input voltage	100 - 240 V
Output voltage	12 V DC
Operating temperature range	10 °C...40 °C
Storage temperature range	-10 °C...80 °C
Packs of	1 pc(s).
Net weight	0.254 kg
Gross weight	0.294 kg
Customs tariff number	85043121
ETIM 9	EC001781
ECLASS 8.0	19089213
Product description	SM Power pack, For TFT-Monitor, Input voltage: 100-240 V, Ausgang: 12 V, L: 1,5 m