## Rittal - The System.

Faster – better – everywhere.





# TP 6705.600 Pedestals

State: 2025.12.14 (Source: rittal.com/lt-en)



#### TP 6705.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

#### **Features**

| Model No.                               | TP 6705.600  |
|---|--|
| Material                                | Enclosure: Sheet steel 1.5 mm                                    |
|   | Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in |
|   | PU seal  |
|   | Mounting plate: Sheet steel                                      |
| Surface finish                          | Enclosure, cover and door: Dipcoat-primed, powder-coated on the  |
|   | outside, textured paint  |
|   | Mounting plate: Zinc-plated                                      |
| Colour                                  | RAL 7035   |
| Supply includes                         | Enclosure open at top  |
|   | Door or double door with locking rod (with depth 400 mm at the   |
|   | front, with depth 500 mm at the front and rear)                  |
|   | Mounting plate   |
|   | Gland plates   |
| Dimensions mounting plate (W x H)       | 699 mm x 571 mm  |
| Number of doors                         | 1  |
| Dimensions                              | Width: 800 mm  |
|   | Height: 675 mm   |
|   | Depth: 500 mm  |
| IP protection category to IEC 60<br>529 | IP 55  |
| Protection category NEMA                | NEMA 12  |
| Note                                    | Mounting plate, depth-variable on a 25 mm pitch pattern          |
| Packs of                                | 1 pc(s).   |
| Net weight                              | 51   |
|   |  |

© Rittal 2025

### **Features**

| Gross weight          | 52.5          |
|-----------------------|---------------|
| Customs tariff number | 94032080      |
| EAN                   | 4028177959897 |
| ETIM 9                | EC000784      |
| ETIM 8                | EC000784      |
| ECLASS 8.0            | 27180504      |

## **Approvals**

| Approvals    | UL + C-UL (listed)           |
|--------------|------------------------------|
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |

© Rittal 2025 3